

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0675820000](#)  
**Status:** **Active**  
**Overview:** [Serial ATA Connectors and Cable Assemblies](#)  
**Description:** 1.27mm Pitch Crimp Housing for Serial ATA Power Cable Receptacle, 15 Circuits, Black

**Documents:**

[3D Model](#) [Packaging Specification PK-67582-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-67490-002-001 \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family Crimp Housings  
 Series [67582](#)  
 Application Power, Wire-to-Board  
 Overview [Serial ATA Connectors and Cable Assemblies](#)  
 Product Name Serial ATA  
 UPC 800756591391


**Physical**

Circuits (maximum) 15  
 Circuits Detail 5 sets terminal per housing  
 Color - Resin Black  
 Flammability 94V-0  
 Gender Receptacle  
 Glow-Wire Capable No  
 Keying to Mating Part Yes  
 Lock to Mating Part No  
 Material - Resin Polyester  
 Net Weight 2.160/g  
 Number of Rows 1  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 1.27mm  
 Pitch - Termination Interface 1.27mm  
 Polarized to Mating Part No  
 Ports 1  
 Stackable No  
 Temperature Range - Operating -35° to +85°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-67582-001  
 Product Specification PS-67490-002-001  
 Sales Drawing SD-67582-001



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/61/2018 (27 June  
 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[67582](#) Series

**Use With**

[67581](#) Crimp Terminals