

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0738380007

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm SL Crimp Housing, Single Row, Version N, TPA with Positive Latch, 7 Circuits, Natural

Documents:

3D Model

Drawing (PDF)

Product Specification PS-73838-005-001 (PDF)

Packaging Specification PK-70873-0540 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

Crimp Housings

73838

Signal, Wire-to-Board, Wire-to-Wire

Terminal Position Assurance (TPA) Piece

SL Modular Connectors

SL

800754789509

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Stackable

Temperature Range - Operating

7

Natural

Receptacle

No

Polyester Alloy

0.158/g

1

Bag

No

2.54mm

No

-40° to +105°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-70873-0540

PS-73838-005-001

SD-73838-004



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2018 (15

January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73838 Series

Mates With

70018 , 70543, 70545 , 70553 , 70555,

70107 Version A, 70107 Version B

Use With

70058 , 71851 , 73838

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION