

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008650115](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK 396 Crimp Terminal 2478, 18-24 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [2478](#)
 Application Power, Wire-to-Board
 Crimp Quality Equipment Yes
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-65-0114 \(Reel\)](#)
 Product Name KK 396, KK 508
 UPC 800754227230

Physical

Gender Female
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Gold
 Net Weight 0.150/g
 Packaging Type Bag
 Plating min - Mating 0.381µm
 Plating min - Termination 0.381µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 2.79mm max.
 Wire Size AWG 18, 20, 22, 24
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 2478-3-(555)L

Reference - Drawing Numbers

Packaging Specification PK-2759-001
 Product Specification PS-08-50-001
 Sales Drawing SD-2478-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2478 Series](#)

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,
[5239](#)