

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0932870001](#)
Status: **Active**
Overview: SRC - Sealed Rectangular Connectors
Description: SRC Housing, Female, 84 Pin Signal (84 x MX150), SPS/Nylon, Black

Documents:

Drawing (PDF)	Packaging Specification 937320001-K (PDF)
Product Specification 850700010-K (PDF)	Test Summary STR-1389-001 (PDF)
Product Specification 850830010-P (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 937320001-P (PDF)	Product Literature (PDF)
Application Specification 850830010-A (PDF)	



General

Product Family	Crimp Housings
Series	93287
Application	Signal, Wire-to-Wire
More Detailed Tech Information	Current (max.) for 84 way fully loaded 6A with 30° temp rise (AWG 14 MX150)
Overview	SRC - Sealed Rectangular Connectors
Product Literature Order No	987650-7391
Product Name	SRC
UPC	884982405226

Physical

Circuits (maximum)	84
Circuits Detail	84 x MX150™
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	121.830/g
Number of Rows	14
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	850830010-A
Packaging Specification	937320001-K
Product Specification	850700010-K, 850830010-P, 937320001-P
Sales Drawing	932870001-000
Test Summary	STR-1389-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93287 Series](#)

Mates With

SRC Signal Blade Housing [93288-0001](#) , [93792-8400](#)

Use With

MX150 Female Terminals [33012](#)