


Evofire 70mm cutout Fire Rated Downlight Round Satin Nickel with GU10 Holder

Partcode: ILDLFR70D002 / Page: 1



The Evofire Fire Rated Downlight is a safe and attractive fitting for a GU10 LED lamp. The fully open design of the Evofire does not conceal your lamp in a large metal canister, which can trap some of the heat it generates, lowering lamp lifetime and performance. Lamps installed in an Evofire run at up to 10 degrees C cooler than a typical can-style fire rated downlight from leading LED brands - this can extend the lifetime of your lamps.

As well being very tough thanks to its steel construction, The Evofire is also a highly aesthetic choice for Fire Rated lighting. The 1mm blend-in bezel is up to 10 times thinner than typical IP65 rated downlights and fits almost flush with your ceiling, so the downlight looks discreet and pleasing in any setting. The satin nickel finish on this model looks stylish and contemporary.

This downlight is fire rated to 30, 60 and 90 minutes in compliance with BS476 Part 21:1987, Air Tightness compliant with Part C and Part L and Resistance to Sound compliant with Part E. See installation guide for full details.

[Watch Video](#)

Evofire shown with Real Colour GU10 LED lamp (sold separately).

Product Details

Partcode: ILDLFR70D002

Check Code: 136029

Range Name: EVOFIRE

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: Fire Rated

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Material: Steel, Glass

Construction: Pressed Steel, Glass

Partcode: ILDLFR70D002 / Page: 2

Physical Data

Length: 39mm

Diameter: 85mm

Weight (Unpackaged Single Unit): 70g

Cut Out Diameter: 70mm

Lamp or Luminaire Shape: Round

Luminaire Fixing: Recess mounted

Fire Rating: 30, 60, 90

Electrical Data

Environmental

IP (Ingress Protection) Rating: IP65

IP Rating (Back/Recessed side): IP20

Packaging



EAN Barcode (unit of 1): 5055788228387

Packaged Weight (Unit of 1): 170g

Length (unit of 1): 90mm

Width (unit of 1): 90mm

Depth (unit of 1): 65mm

Outer packaging info available on website

Product data last updated on: Thursday, October 25, 2018 - 16:12