



Mobile Chip LED Light ML CN 130 V2 IP 65


For outdoor use.

30 W high power Chip LED Light for wall installation, with extra-wide light diffusion to illuminate a large area.

- Low heat generation, no danger of injury.
- Chip LEDs have an extremely long lifespan, are shock-proof, maintenance-free.
- Die-cast aluminium casing.
- Stable, shock-absorbing steel-tube frame with ergonomic carrying handle.
- Spotlight mechanism can be swivelled and locked.
- With safety glass.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.
- Energy efficiency class: A+

NEW



Article No.	EAN-Code 4007123...	UP	Cable length	Cable	Power	Luminous flux	Lamp efficacy	Colour temperature	Plug
1 17125 3 323	640096	1	5 m	H07RN-F 3G1.0	30 W	2550 lm	88 lm/W	6500 K	BS 1363 
1 17125 3 333	640102	1	5 m	H07RN-F 3G1.0	30 W	2550 lm	88 lm/W	6500 K	110 V 