

## LED Light JARO

For indoor and outdoor use, IP 65.

- LED light with ultra-bright Everlight SMD LEDs.
- Easy to mount thanks to external water-tight terminal clamp.
- With safety glass.
- Solid, modern aluminium housing.
- With adjustable mounting bracket for mounting.



Article No.	Barcode (4007123...)	UP	LEDs	Power	Luminous flux	Efficacy	Measurements
1171250131	656257	1	14	10 W	900 lm	91 lm/W	138 x 69 x 143 mm
1171250231	656288	1	28	20 W	1870 lm	95 lm/W	179 x 71 x 186,5 mm
1171250331	656301	1	44	30 W	2930 lm	95 lm/W	229 x 72,5 x 255 mm
1171250531	656332	1	75	50 W	4770 lm	98 lm/W	263 x 83 x 291 mm
1171250831	656363	1	120	80 W	7200 lm	91 lm/W	273 x 60 x 310 mm
1171250031	656387	1	150	100 W	8850 lm	92 lm/W	308 x 60 x 345 mm

This light includes integrated LED lamps. The lamps in the light cannot be exchanged.

Available from: September