

SAFETY, FACILITY & EQUIPMENT
IDENTIFICATION

BradyID.com/s35

Your experts
for safety,
facility and
equipment
identification.





Compact Safety Padlock Kits

Ideal for any worker needing just "one lock and one tag"

- 1 - Compact Safety Padlock
- 1 - Reuseable Heavy-duty Laminated Polyester (B-837) Lockout Tag
- 1 - Nylon Cable Tie

Compact Safety Padlock Kits

Catalog #	Lock Color	Qty
123143	Red	1
123144	Green	1
123145	Orange	1
123146	Blue	1
123147	Yellow	1
123148	Brown	1
123149	White	1
123150	Purple	1
123151	Black	1

new



Compact Cable Padlocks

- Compact 1.31"x1.25" nylon body with an elongated, flexible cable as the shackle
- Flexible cable means you can angle and twist padlock or lockout multiple energy isolation points with one lock

Compact Cable Padlocks

Color	Cable Length	1 Pack Keyed Different	6 Pack Keyed Alike
Red	Short 7.87" (20 cm)	146120	146128
Red	Long 15.75" (40 cm)	146124	146132
Yellow	Short 7.87" (20 cm)	146121	146129
Yellow	Long 15.75" (40 cm)	146125	146133
Blue	Short 7.87" (20 cm)	146122	146130
Blue	Long 15.75" (40 cm)	146126	146134
Green	Short 7.87" (20 cm)	146123	146131
Green	Long 15.75" (40 cm)	146127	146135



Safety Padlocks with Non-Conductive Nylon Shackle

- Lightweight, non-conductive and non-sparking body
- Special 6-pin cylinder resists tampering
- Fiberglass reinforced nylon body with non-conductive nylon shackle
- Lock body dimensions: 1-3/4"H x 1-1/2"W x 4/5"D
- Shackle clearance: 1-1/2"; shackle diameter: 1/4"
- Each padlock includes 1 key and 1 each English, Spanish and French labels

Safety Padlocks - 1-1/2" Nylon Shackle

Color	Keyed Different 1/Pack	Keyed Different 6/Pack	Keyed Alike 3/Pack	Keyed Alike 6/Pack
Red	123324	123351	123333	123342
Green	123326	123353	123335	123344
Orange	123328	123355	123337	123346
Blue	123325	123352	123334	123343
Yellow	123327	123354	123336	123345
Brown	123330	123357	123339	123348
White	123332	123359	123341	123350
Purple	123331	123358	123340	123349
Black	123329	123356	123338	123347



3" Lock Body!

Long Body Safety Padlocks

- 3" long body has ample space for your most important identification information
- Lightweight, non-conductive and non-sparking body
- Special 6-pin cylinder resists tampering
- Fiberglass reinforced nylon body and triple-coated hardened steel shackle
- Service temperature: 0°–250° F (-20°–120°C)
- Lock body dimensions: 3"H x 1-1/2"W x 4/5"D
- Shackle clearance: 1-1/2"; shackle diameter: 1/4"
- Each padlock includes 1 key and 1 each English/Spanish and English/French labels

Long Body Safety Padlocks - 1-1/2" Shackle

Color	Keyed Different 1/Pack	Keyed Different 6/Pack	Keyed Alike 3/Pack	Keyed Alike 6/Pack
Red	123405	123396	123414	123423
Green	123407	123398	123416	123425
Orange	123409	123400	123418	123427
Blue	123406	123397	123415	123424
Yellow	123408	123399	123417	123426
Brown	123411	123402	123420	123429
White	123413	123404	123422	123431
Purple	123412	123403	123421	123430
Black	123410	123401	123419	123428

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.

Lockout Tagout