



/Dimensions : 56x165.5x8.5mm  
 /1 Terminal Strips Strip : 630 Tie-point  
 2 Distribution Strips : 200 Tie-point  
 /Pitch: 2.54mm  
 /Material  
 /Housing : ABS plastic  
 /Spring Clips : Brass, Ni plated  
 /Wire range : Sol 20~29AWG  
 /Rated voltage : 300V  
 /Rated current : 3~5A  
 /Printing: A,B,C.....I,J 0,5,10,15,20.....55,60  
 /Color: 黑色/Black,字体/Fonts: 方正黑体,  
 /Height: 1.5mm,字宽系数/Width: 1.0  
 /Jumper Wires  
 140pcs of 22AWG solid wires  
 Per-cut, Pre Stripped and Pre-formwd  
 on each end.  
 Variety color  
 14 lengths x 10pcs each  
 (2\5\7\10\12\15\17\20\22\25\50\75\100  
 and 125mm)

		linear dimension(Tolerances Standard GB/T 14486-2008)										≡	—	□	//	⊥	
variable range	to	over 6 to 10	over 10 to 18	over 18 to 30	over 30 to 50	over 50 to 80	over 80 to 120	over 120 to 160	over 160 to 200	over 200 to 250	all	to 5	over 5 to 30	over 30 to 120	over 120 to		
tolerance		±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12	0.4

单位 / UNITS	mm	尺寸 / SIZE	A4	比例 / SCALE	1:1.8	第三视角/THIRD ANGLE PROJECTION
						TITLE
						BB-102+J