



REVISION RECORD			
REV.	CONTENT	MOD.	DATE
△	New Publish		



B



Section A-A

View B

Notes:

1. Pitch: 2.54mm
- 2.1 Terminal Strip: 300 Tie-point
- 3.2 Distribution Strips: 100 Tie-point
4. Rated voltage/current: 300V / 3-5A
5. Insulation resistance: 500MΩ/DC500V
6. Withstanding voltage: AC1000V/1Min
7. Wire range: 29~20 AWG
8. Temp. Range: -25° c~+80° c

Strip length: 7-8mm

9. Undimensioned Tolerances:

TOLERANCES EXCEPT AS NOTED

variable range	linear dimension				fillet	chamfer	∠short angle sid				≡	—	□	//	⊥	
	to 6	over 6 to 30	over 30 to 120	over 120 to 480			all	to 6	to 10	to 50						to 120
tolerance	±0.1	±0.2	±0.3	±0.5	±0.2	±0.5	±1	1°	30'	20'	10'	0.5	0.025	0.06	0.12	0.4

2	BB-801-2-72	702817201A	1	Terminal Strip
1	BB-801-1-72	702717201A	2	Distribution Strips
NO.	NAME OF PART	NO. OF PART	Q'TY	NOTES
DES.	YYS	DATE	09/03/11"	UNITS mm
CHK.	DATE	SIZE	A4	FIRST ANGLE PROJECTION
APP.	DATE	SCALE	1:1	DWG NO. SP-2-7030001
TITLE				BB-801T
				BB-801T(72 Transparent)