


- /Dimensions : 201.5x220.2x8.3mm
- /7 Distribution Strip : 700 Tie-point
- 4 Terminal Strip: 2560 Tie-point
- /4 Binding Posts
- /Blue Plastic Plate:235.3x256x18mm
- /Material
- /Housing : ABS plastic
- /Spring Clips : Brass, Ni plated
- /Screws: M2.5 Steel Paint plated
- /Wire range : Sol 29~20AWG
- /Rated voltage : 300V
- /Rated current : 3~5A
- /Print
- /Color:白色/White



		linear dimension(Tolerances Standard GB/T 14486-2008)										≡	—	□	//	⊥
variable range	to	over 6 to 10	over 10 to 18	over 18 to 30	over 30 to 50	over 50 to 80	over 80 to 120	over 120 to 160	over 160 to 200	over 200 to 250	all	to 5	over 5 to 30	over 30 to 120	over 120 to	
	tolerance	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12

单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	1:2.5	第三视角/THIRD ANGLE PROJECTION
名称/TITLE	PR-4T7D-02未包装					