

KEMET, EFF4, Flex Suppressors, Noise Suppression



General Information

Series:	EFF4
Style:	Sheet
Description:	Flex Suppressor Flame Retardant Type
Features:	Flame Retardant Type
RoHS:	Yes
Qualifications:	UL94 V-0, UL File No.E176124, AEC-Q200
Environment:	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions

Sheet Size	120x120mm
L	120mm NOM
W	120mm NOM
T	0.2mm NOM

Specifications

Temperature Range:	-40/+125C
Magnetic Permeability:	140 u At 3MHz
Effective Frequency:	10 GHz MAX
Resistance:	1 MOhms MIN
Specific Gravity:	3.7 Atm TYP

Packaging Specifications

Weight:	11.24 g
---------	---------