



www.y3k.com

Model: IQC1080PIRQ



IQCCTV 1080P AHD/CVI/TVI Hybrid Covert PIR Camera, UTC

Model: IQC1080PIRQ	
Style	Covert Camera
Weather Resistant	No
Vandal Resistant	No
Mounting Type	Wall
Sensor	1/2.8" Sony 2.43 Megapixel Sensor
DSP Type	IQCCTV DSP
DSP Functions	Backlight Compensation, White Balance, Day/Night, DWDR, DNR
Video Formats Supported	AHD 1080P, HD-TVI, HD-CVI, 960H
Resolution	1080P
Lens Type	Fixed
Lens Size	3.7mm
Viewing Angle	78°
Night Vision	No
Minimum Illumination	0.03 Lux
Operating Voltage	12V DC
Video Output	BNC Socket

Audio Output	Yes
Power Input	DC Socket (2.1mm)
RS485 Control	No
Operating Temperature	-10 - 55°
Dimensions (WHD)	60x103x60mm
Weight (kg)	0.10
Warranty	1 Year Warranty