

Order symbol: ARK14127CHLT
Product nbr: 8561583
Description: PC Enclosure
Remarks: Hinged transparent cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs.

EAN: 6418074097590
EI. number:
Finland:

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

| Dimensions: | | | | Accessories: | |
|-------------------------------------|--------------------------|-------|--------|---|-----------------------------|
| | Length | Width | Height | | |
| mm: | 356 | 305 | 178 | ALBP1412 | Aluminum Back Panel |
| inch: | 14.0 | 12.0 | 7.0 | ADFP1412 | Dead Front Panel w/ screws |
| Materials: | | | | ASP1412 | Aluminum Swing Panel |
| Material: | Polycarbonate | | | ASPK1412 | Swing Panel Kit incl. Panel |
| Base colour: | RAL 7035 -light grey | | | ASPHK14 | Swing Panel Kit w/o Panel |
| Cover screws material: | Stainless steel | | | AMFL12 | 12" Mounting Flange Set |
| Cover colour: | Clear transparent | | | Rating: | |
| Gasket material: | Polyurethane | | | Ingress Protection (EN 60529): IP66/IP67 | |
| Temperatures: | | | | Impact Resistance (EN 62262): IK09 | |
| Temperature °C (short term): | -40 ... 140 °C | | | Electrical insulation: Totally insulated | |
| Temperature °C (continuous): | -40 ... 80 °C | | | Halogen free (DIN/VDE 0472, Part 815): 1 | |
| Temperature °F (short term): | -40 ... 284 °F | | | UV resistance: UL 508 | |
| Temperature °F (continuous): | -40 ... 175 °F | | | Flammability Rating: UL 508 | |
| Accessories: | | | | Glow Wire Test (IEC 695-2-1) °C: 960 | |
| ABP1412 | Painted Steel Back Panel | | | NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13 | |

