

Order symbol: ARK14127CHLTM
Product nbr: 8561585
Description: PC Enclosure
Remarks: Hinged transparent cover
w/Plastic quick release latch.
Base includes 1/2 and 3/4 inch
knock-outs and metal mounting
feet.

EAN: 6418074097613
El. number:
Finland:

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Accessories:	
mm:	356	305	178	ALBP1412	Aluminum Back Panel
inch:	14.0	12.0	7.0	ADFP1412	Dead Front Panel w/ screws
				ASP1412	Aluminum Swing Panel
				ASPK1412	Swing Panel Kit incl. Panel
				ASPHK14	Swing Panel Kit w/o Panel
				AMFL12	12" Mounting Flange Set
Materials:					
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Stainless steel				
Cover colour:	Clear transparent				
Gasket material:	Polyurethane				
Temperatures:					
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP1412		Painted Steel Back Panel			

Rating:

Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK09
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 508
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13

