

Order symbol: ARK865CHSCT
Product nbr: 8561427
Description: PC Enclosure
Remarks: Hinged transparent screw cover, base includes 1/2 and 3/4 inch knock-outs.

EAN: 6418074096036
El. number:
Finland:

Including: Hinged screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
mm:	203	152	127	ALBP86	Aluminum Back Panel
inch:	8.0	6.0	5.0	ADFP86	Dead Front Panel w/ screws
				ASP86	Aluminum Swing Panel
Materials:				ASPK86	Swing Panel Kit incl. Panel
Material:	Polycarbonate			ASPHK8	Swing Panel Kit w/o Panel
Base colour:	RAL 7035 -light grey			AMFL6	6" Mounting Flange Set
Cover screws material:	Stainless steel				
Cover colour:	Clear transparent				
Gasket material:	Polyurethane				
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 140 °C			Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK09	
Temperature °F (short term):	-40 ... 284 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				UV resistance: UL 508	
ABP86	Painted Steel Back Panel			Flammability Rating: UL 508	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	

