

Order symbol:	ARK1086CHTSST
Product nbr:	8561499
Description:	PC Enclosure
Remarks:	Hinged transparent cover w/S.S. Lockable twist latch. Base includes 1/2 and 3/4 inch knock-outs.

EAN: 6418074096753
El. number:
 Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
mm:	254	203	152	ALBP108	Aluminum Back Panel
inch:	10.0	8.0	6.0	ADFP108	Dead Front Panel w/ screws
Materials:			ASP108	Aluminum Swing Panel	
			ASPK108	Swing Panel Kit incl. Panel	
			ASPHK10	Swing Panel Kit w/o Panel	
			AMFL8	8" Mounting Flange Set	
Material:	Polycarbonate		Rating:		
Base colour:	RAL 7035 -light grey		Ingress Protection (EN 60529): IP66/IP67		
Cover screws material:	Stainless steel		Impact Resistance (EN 62262): IK09		
Cover colour:	Clear transparent		Electrical insulation: Totally insulated		
Gasket material:	Polyurethane		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperatures:			UV resistance: UL 508		
			Flammability Rating: UL 508		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13		
Accessories:					
ABP108	Painted Steel Back Panel				

