

ARCA ARK1085CHFL



Order symbol:	ARK1085CHFL
Product nbr:	8561454
Description:	PC Enclosure
Remarks:	Hinged opaque flat cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs

EAN: 6418074096302
El. number:
 Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

Dimensions:	Length	Width	Height
mm:	254	203	127
inch:	10.0	8.0	5.0
Materials:			
Material:	Polycarbonate		
Base colour:	RAL 7035 -light grey		
Cover screws material:	Stainless steel		
Cover colour:	RAL 7035 -light grey		
Gasket material:	Polyurethane		
Temperatures:			
Temperature °C (short term):	-40 ... 140 °C		
Temperature °C (continuous):	-40 ... 80 °C		
Temperature °F (short term):	-40 ... 284 °F		
Temperature °F (continuous):	-40 ... 175 °F		
Accessories:			
ABP108	Painted Steel Back Panel		

