

Order symbol: ARK865CHLM
Product nbr: 8561420
Description: PC Enclosure
Remarks: Hinged opaque cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs and metal mounting feet

EAN: 6418074095961
El. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:	
mm:	203	152	127	ALBP86	Aluminum Back Panel
inch:	8.0	6.0	5.0	ADFP86	Dead Front Panel w/ screws
				ASP86	Aluminum Swing Panel
				ASPK86	Swing Panel Kit incl. Panel
				ASPHK8	Swing Panel Kit w/o Panel
				AMFL6	6" Mounting Flange Set
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529):	IP66/IP67
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262):	IK09
Cover screws material:	Stainless steel			Electrical insulation:	Totally insulated
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815):	1
Gasket material:	Polyurethane			UV resistance:	UL 508
				Flammability Rating:	UL 508
				Glow Wire Test (IEC 695-2-1) °C:	960
				NEMA Class:	UL Type 4, 4X, 6, 6P, 12 and 13
Temperatures:					
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP86	Painted Steel Back Panel				

