



Order symbol: ARK1085CHFSC
Product nbr: 8561457
Description: PC Enclosure
Remarks: Hinged opaque flat screw cover, base includes 1/2 and 3/4 inch knock-outs

EAN: 6418074096333
El. number:
Finland:

Including: Hinged screw flat cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

| Dimensions: | | | Accessories: | | |
|------------------------------|--------------------------|-------|--------------|--|-----------------------------|
| mm: | Length | Width | Height | | |
| mm: | 254 | 203 | 127 | ALBP108 | Aluminum Back Panel |
| inch: | 10.0 | 8.0 | 5.0 | ADFP108 | Dead Front Panel w/ screws |
| | | | | ASP108 | Aluminum Swing Panel |
| | | | | ASPK108 | Swing Panel Kit incl. Panel |
| | | | | ASPHK10 | Swing Panel Kit w/o Panel |
| | | | | AMFL8 | 8" Mounting Flange Set |
| Materials: | | | | Rating: | |
| Material: | Polycarbonate | | | Ingress Protection (EN 60529): IP66/IP67 | |
| Base colour: | RAL 7035 -light grey | | | Impact Resistance (EN 62262): IK09 | |
| Cover screws material: | Stainless steel | | | Electrical insulation: Totally insulated | |
| Cover colour: | RAL 7035 -light grey | | | Halogen free (DIN/VDE 0472, Part 815): 1 | |
| Gasket material: | Polyurethane | | | UV resistance: UL 508 | |
| Temperatures: | | | | Flammability Rating: UL 508 | |
| Temperature °C (short term): | -40 ... 140 °C | | | Glow Wire Test (IEC 695-2-1) °C: 960 | |
| Temperature °C (continuous): | -40 ... 80 °C | | | NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13 | |
| Temperature °F (short term): | -40 ... 284 °F | | | Certificates: | |
| Temperature °F (continuous): | -40 ... 175 °F | | | Gost R | |
| Accessories: | | | | | |
| ABP108 | Painted Steel Back Panel | | | | |

