



Order symbol: ARK12105CHFLM
Product nbr: 8561510
Description: PC Enclosure
Remarks: Hinged opaque flat cover
w/Plastic quick release latch.
Base includes 1/2 and 3/4 inch
knock-outs and metal mounting
feet

EAN: 6418074096869
El. number:
Finland:

Sample photo

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
Length	Width	Height	ALBP1210	Aluminum Back Panel	
mm:	305	254	ADFP1210	Dead Front Panel w/ screws	
inch:	12.0	10.0	ASP1210	Aluminum Swing Panel	
Materials:			ASPK1210	Swing Panel Kit incl. Panel	
Material:	Polycarbonate		ASPHK12	Swing Panel Kit w/o Panel	
Base colour:	RAL 7035 -light grey		AMFL10	10" Mounting Flange Set	
Cover screws material:	Stainless steel		Rating:		
Cover colour:	RAL 7035 -light grey		Ingress Protection (EN 60529): IP66/IP67		
Gasket material:	Polyurethane		Impact Resistance (EN 62262): IK09		
Temperatures:			Electrical insulation: Totally insulated		
Temperature °C (short term):	-40 ... 140 °C		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °C (continuous):	-40 ... 80 °C		UV resistance: UL 508		
Temperature °F (short term):	-40 ... 284 °F		Flammability Rating: UL 508		
Temperature °F (continuous):	-40 ... 175 °F		Glow Wire Test (IEC 695-2-1) °C: 960		
Accessories:			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13		
ABP1210	Painted Steel Back Panel		Certificates:		
			Gost R		

