



Order symbol: ARK1085CHFSSF
Product nbr: 8561461
Description: PC Enclosure
Remarks: Hinged opaque flat cover w/S.S.
 Quick release latch, base includes 1/2 and 3/4 inch knock-outs, plastic mounting flanges

EAN: 6418074096371
El. number:
Finland:

Sample photo

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
mm:	254	203	127	ALBP108	Aluminum Back Panel
inch:	10.0	8.0	5.0	ADFP108	Dead Front Panel w/ screws
				ASP108	Aluminum Swing Panel
Materials:				ASPK108	Swing Panel Kit incl. Panel
Material:	Polycarbonate			ASPHK10	Swing Panel Kit w/o Panel
Base colour:	RAL 7035 -light grey			AMFL8	8" Mounting Flange Set
Cover screws material:	Stainless steel				
Cover colour:	RAL 7035 -light grey			Rating:	
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
Temperatures:				Impact Resistance (EN 62262): IK09	
Temperature °C (short term):	-40 ... 140 °C			Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 284 °F			UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 508	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
ABP108	Painted Steel Back Panel			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
				Certificates:	
				Gost R	

