



Order symbol: ARK864CHFLM
Product nbr: 8561402
Description: PC Enclosure
Remarks: Hinged opaque flat cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs and metal mounting feet

EAN: 6418074095787
El. number:
Finland:

Sample photo

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:	
mm:	203	152	101	ALBP86	Aluminum Back Panel
inch:	8.0	6.0	4.0	ADFP86	Dead Front Panel w/ screws
				ASP86	Aluminum Swing Panel
				ASPK86	Swing Panel Kit incl. Panel
				ASPHK8	Swing Panel Kit w/o Panel
				AMFL6	6" Mounting Flange Set
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK09	
Cover screws material:	Stainless steel			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Gasket material:	Polyurethane			UV resistance: UL 508	
Temperatures:				Flammability Rating: UL 508	
Temperature °C (short term):	-40 ... 140 °C			Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °C (continuous):	-40 ... 80 °C			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:				Certificates:	
ABP86		Painted Steel Back Panel		Gost R	

