

Order symbol: ARK14127CHSSTM
Product nbr: 8561603
Description: PC Enclosure
Remarks: Hinged transparent cover w/S.S. Quick release latch, base includes 1/2 and 3/4 inch knock-outs, metal mounting feet.

EAN: 6418074097798
El. number:
Finland:

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	356	305	178	ALBP1412	Aluminum Back Panel
inch:	14.0	12.0	7.0	ADFP1412	Dead Front Panel w/ screws
				ASP1412	Aluminum Swing Panel
				ASPK1412	Swing Panel Kit incl. Panel
				ASPHK14	Swing Panel Kit w/o Panel
				AMFL12	12" Mounting Flange Set
Rating:					
Ingress Protection (EN 60529): IP66/IP67					
Impact Resistance (EN 62262): IK09					
Electrical insulation: Totally insulated					
Halogen free (DIN/VDE 0472, Part 815): 1					
UV resistance: UL 508					
Flammability Rating: UL 508					
Glow Wire Test (IEC 695-2-1) °C: 960					
NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13					
Accessories:					
ABP1412		Painted Steel Back Panel			

