

Order symbol: ARK1086CHLF
Product nbr: 8561473
Description: PC Enclosure
Remarks: Hinged opaque cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs and plastic mounting flanges

EAN: 6418074096494
El. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	254	203	152	ALBP108 Aluminum Back Panel
inch:	10.0	8.0	6.0	ADFP108 Dead Front Panel w/ screws
			ASP108 Aluminum Swing Panel	
			ASPK108 Swing Panel Kit incl. Panel	
			ASPHK10 Swing Panel Kit w/o Panel	
			AMFL8 8" Mounting Flange Set	
Materials:			Rating:	
Material:	Polycarbonate		Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK09	
Cover screws material:	Stainless steel		Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1	
Gasket material:	Polyurethane		UV resistance: UL 508	
Temperatures:			Flammability Rating: UL 508	
Temperature °C (short term):	-40 ... 140 °C		Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °C (continuous):	-40 ... 80 °C		NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
Temperature °F (short term):	-40 ... 284 °F			
Temperature °F (continuous):	-40 ... 175 °F			
Accessories:				
ABP108	Painted Steel Back Panel			

