



Order symbol: ARK14126CHFSSM
Product nbr: 8561573
Description: PC Enclosure
Remarks: Hinged opaque flat cover w/S.S. latch. Base includes 1/2 and 3/4 inch knock-outs and metal mounting feet.

EAN: 6418074097491
El. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

Dimensions:			Accessories:		
mm:	305	254	127	ALBP1412	Aluminum Back Panel
inch:	12.0	10.0	5.0	ADFP1412	Dead Front Panel w/ screws
			ASP1412	Aluminum Swing Panel	
Materials:			ASPK1412	Swing Panel Kit incl. Panel	
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Stainless steel				
Cover colour:	RAL 7035 -light grey				
Gasket material:	Polyurethane				
Temperatures:					
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP1412	Painted Steel Back Panel				

