

Order symbol: ARK14127CHSCTM
Product nbr: 8561591
Description: PC Enclosure
Remarks: Hinged transparent screw cover, base includes 1/2 and 3/4 inch knock-outs and metal mounting feet.

EAN: 6418074097675
El. number:
Finland:

Including: Hinged screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
mm:	356	305	178	ALBP1412	Aluminum Back Panel
inch:	14.0	12.0	7.0	ADFP1412	Dead Front Panel w/ screws
			ASP1412	Aluminum Swing Panel	
Materials:			ASPK1412	Swing Panel Kit incl. Panel	
Material:	Polycarbonate		ASPHK14	Swing Panel Kit w/o Panel	
Base colour:	RAL 7035 -light grey		AMFL12	12" Mounting Flange Set	
Cover screws material:	Stainless steel				
Cover colour:	Clear transparent				
Gasket material:	Polyurethane				
Temperatures:			Rating:		
Temperature °C (short term):	-40 ... 140 °C		Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (continuous):	-40 ... 80 °C		Impact Resistance (EN 62262): IK09		
Temperature °F (short term):	-40 ... 284 °F		Electrical insulation: Totally insulated		
Temperature °F (continuous):	-40 ... 175 °F		Halogen free (DIN/VDE 0472, Part 815): 1		
			UV resistance: UL 508		
			Flammability Rating: UL 508		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		
Accessories:					
ABP1412	Painted Steel Back Panel				

