

**Order symbol:** ARK14127CHL      **EAN:** 6418074097569  
**Product nbr:** 8561580      **El. number:**  
**Description:** PC Enclosure      **Finland:**  
**Remarks:** Hinged opaque cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

| Dimensions:                         |                          |       |        | Accessories:                                |                             |
|-------------------------------------|--------------------------|-------|--------|---|-----------------------------|
|                                     | Length                   | Width | Height |   |                             |
| <b>mm:</b>                          | 356                      | 305   | 178    | ALBP1412                                    | Aluminum Back Panel         |
| <b>inch:</b>                        | 14.0                     | 12.0  | 7.0    | ADFP1412                                    | Dead Front Panel w/ screws  |
| <b>Materials:</b>                   |                          |       |        | ASP1412                                     | Aluminum Swing Panel        |
| <b>Material:</b>                    | Polycarbonate            |       |        | ASPK1412                                    | Swing Panel Kit incl. Panel |
| <b>Base colour:</b>                 | RAL 7035 -light grey     |       |        | ASPHK14                                     | Swing Panel Kit w/o Panel   |
| <b>Cover screws material:</b>       | Stainless steel          |       |        | AMFL12                                      | 12" Mounting Flange Set     |
| <b>Cover colour:</b>                | Clear transparent        |       |        | <b>Rating:</b>                              |                             |
| <b>Gasket material:</b>             | Polyurethane             |       |        | Ingress Protection (EN 60529): IP66/IP67    |                             |
| <b>Temperatures:</b>                |                          |       |        | Impact Resistance (EN 62262): IK09          |                             |
| <b>Temperature °C (short term):</b> | -40 ... 140 °C           |       |        | Electrical insulation: Totally insulated    |                             |
| <b>Temperature °C (continuous):</b> | -40 ... 80 °C            |       |        | Halogen free (DIN/VDE 0472, Part 815): 1    |                             |
| <b>Temperature °F (short term):</b> | -40 ... 284 °F           |       |        | UV resistance: UL 508                       |                             |
| <b>Temperature °F (continuous):</b> | -40 ... 175 °F           |       |        | Flammability Rating: UL 508                 |                             |
| <b>Accessories:</b>                 |                          |       |        | Glow Wire Test (IEC 695-2-1) °C: 960        |                             |
| ABP1412                             | Painted Steel Back Panel |       |        | NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13 |                             |

