



Order symbol: ARK864CHFTSS
Product nbr: 8561412
Description: PC Enclosure
Remarks: Hinged opaque flat cover w/S.S.
 Lockable twist latch, base
 includes 1/2 and 3/4 inch
 knock-outs

EAN: 6418074095886
El. number:
 Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Sample photo

Dimensions:	Length	Width	Height	Accessories:	
mm:	203	152	101	ALBP86	Aluminum Back Panel
inch:	8.0	6.0	4.0	ADFP86	Dead Front Panel w/ screws
				ASP86	Aluminum Swing Panel
				ASPK86	Swing Panel Kit incl. Panel
				ASPHK8	Swing Panel Kit w/o Panel
				AMFL6	6" Mounting Flange Set
Materials:					
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Stainless steel				
Cover colour:	RAL 7035 -light grey				
Gasket material:	Polyurethane				
Temperatures:					
Temperature °C (short term):	-40 ... 140 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 284 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
ABP86		Painted Steel Back Panel			
Rating:					
				Ingress Protection (EN 60529): IP66/IP67	
				Impact Resistance (EN 62262): IK09	
				Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 508	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
Certificates:					
				Gost R	

