

Order symbol: ARK1086CHSS
Product nbr: 8561484
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
 Quick release latch, base
 includes 1/2 and 3/4 inch
 knock-outs

EAN: 6418074096609
El. number:
Finland:

Including: Hinged cover. Base with 10-32 brass inserts, latched cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:		Length	Width	Height	Accessories:	
mm:		254	203	152	ALBP108	Aluminum Back Panel
inch:		10.0	8.0	6.0	ADFP108	Dead Front Panel w/ screws
					ASP108	Aluminum Swing Panel
					ASPK108	Swing Panel Kit incl. Panel
					ASPHK10	Swing Panel Kit w/o Panel
					AMFL8	8" Mounting Flange Set
Materials:						
Material:		Polycarbonate				
Base colour:		RAL 7035 -light grey				
Cover screws material:		Stainless steel				
Cover colour:		RAL 7035 -light grey				
Gasket material:		Polyurethane				
Temperatures:						
Temperature °C (short term):		-40 ... 140 °C				
Temperature °C (continuous):		-40 ... 80 °C				
Temperature °F (short term):		-40 ... 284 °F				
Temperature °F (continuous):		-40 ... 175 °F				
Accessories:						
ABP108		Painted Steel Back Panel				

