



Tapered nose for easy working and close tip cutting in confined areas. Convenient .030-Inch and .045-Inch (1 mm) stripping holes. "V" stripping notch in jaw for quick insulation slitting. Serrated behind the hinge to crush insulation.

## Specifications

<b>Type:</b>	Diagonal-Cutting Telephone Work Pliers	<b>Overall Length:</b>	6.125" (155.6 mm)
<b>Jaw Length:</b>	0.813" (20.7 mm)	<b>Jaw Width:</b>	0.75" (19.1 mm)
<b>Jaw Thickness:</b>	13/16" (20.6 mm)	<b>Cutting Knives:</b>	Standard
<b>Cut Style:</b>	Standard	<b>Handle Colour:</b>	Red
<b>Handle Finish:</b>	Plastic-dipped	<b>Weight:</b>	0.33 lb (0.15 kg)