



The dual display CL450 Clamp Meter is a "game changer" for the HVAC professional. This True RMS CAT IV 600V meter offers Differential Temperature, Digital Temperature Calibration, DC Micro Amp, Inrush Current, Audible Continuity, Capacitance, Diode Test, Frequency and Duty Cycle, Low-pass Filter, Low Impedance, AC and DC Current, Min/Max, AVG, Data Hold Capability. Includes carrying case, instruction manual, straight input test leads, two K-type thermocouples and 3 x AAA batteries.

Specifications

Type:	HVAC Clamp Meter with Differential Temperature	Application:	HVAC
Material:	Plastic/electronics	Batteries:	3 x AAA
Auto Shut Off:	Yes	Jaw Size:	2" (50.4 mm)
Drop Protection:	6.6 ft (2 m)	Display:	6,000-count LCD
Voltage:	1000V AC; 1000V DC	Frequency:	999.9kHz
Current:	600A AC	Capacitance:	6000 μ F
Ohms (Resistance):	60M Ω	AC Voltage:	1000
DC Voltage:	1000	DC Polarity Indicator:	Y
DC Microamp:	200 μ A with 1 μ A Resolution	Temperature Range:	-40° to 1832°F (-40° to 1000°C)
Standard:	CATIV 600V, CATIII 1000V	Weight w/batteries:	13.6 oz (386g)
Overall Length:	10" (254.0 mm)	Overall Height:	1.59" (40.4 mm)
Overall Width:	3.77" (95.8 mm)	Weight:	12.5 oz (354 g)