



Easy working in confined areas. Short jaws and beveled cutting edges permit close cutting of wire. Induction-hardened cutting knives for long life. Hot-riveted joint ensures smooth action and no handle wobble. Plastic-dipped handles for comfort and ease of identification. Custom, US-made tool steel.

Specifications

Type:	Standard Diagonal-Cutting Pliers	Application:	Cutting
Overall Length:	6.125" (155.6 mm)	Material:	Steel
Nose Type:	Tapered	Jaw Length:	0.813" (20.7 mm)
Jaw Width:	0.688" (17.5 mm)	Jaw Thickness:	13/16" (20.6 mm)
Jaw Capacity:	1/2" (12.7 mm)	Cutting Knives:	Standard
Cut Style:	Standard	Joint Type:	Hot-Riveted
Handle Colour:	Red	Handle Finish:	Plastic-dipped
Handle Length:	4.938" (125.4 mm)	Insulated:	No
Tether capable:	No	Weight:	0.29 lb (0.13 kg)