



This automatically ranging digital multi-meter measures AC/DC voltage, AC/DC current and resistance. It can also measure temperature, capacitance, frequency, duty-cycle, and test diodes and continuity. Exclusively designed from the ground up, by electricians for electricians.

Specifications

Batteries:	2 x AAA	Drop Protection:	6.6 ft (2 m)
Display:	4,000-count LCD	Functions:	Measures up to 1,000 V AC/DC voltage, 10 A AC/DC current, 40 MΩ resistance, and temperature, capacitance, frequency, duty-cycle, and tests diodes and continuity.
Voltage:	1,000 V AC; 1,000 V DC	Frequency:	1 Hz-500 KHz
Current:	10 A AC; 10 A DC	Capacitance:	1000μF
Ohms (Resistance):	40MΩ	Ingress Protection:	IP42
Standard:	CAT IV 600V / CAT III 1000V	Temperature Range:	0°F-1,000°F (-18°C-538°C)
Included:	Carrying Case, Test Leads, Thermocouple and Batteries	Overall Length:	7" (177.8 mm)
Overall Height:	2.094" (53.2 mm)	Overall Width:	3.547" (90.1 mm)
Weight:	0.90 lb (0.41 kg)		