



This Dual-Range Non-Contact Voltage Tester automatically detects low and standard voltage. A bright-green LED will tell you that the tester is working, and also functions as a work light. The red light flashes and two distinct warning tones sound when either low or standard voltage is detected.

Specifications

Special Features:	50-500 Hz low-pitched pulsing, beeping sound; Blue LED turns off and red LED blinks (approximately twice per second)	Drop Protection:	9.8 ft (3 m)
Voltage:	12 - 1000V AC	Frequency:	50-500 Hz
Pollution Degree:	2	Standard:	CAT IV 1000V
Included:	(2) Alkaline 1.5V AAA batteries	Weight w/batteries:	1.6 oz (45 g)
Batteries:	2 x AAA	Overall Length:	5.5" (139.7 mm)
Overall Height:	1" (25.4 mm)	Overall Width:	0.719" (18.3 mm)
Weight:	0.80 oz (22.7 g)		