

ELECTRONIC SERVICE—CASE SECURITY 6750

A case with the basic equipment of special tools for the installation and maintenance of complex protective devices and alarm systems



6750 **BERNSTEIN SECURITY** with tool set

6755 **BERNSTEIN SECURITY** without tool set

Description:

Case made from deep-drawn, impact-resistant, grained black plastic, with sturdy aluminium frame, dustproof and rainproof, acid- and scratch-resistant. 64 tools are clearly arranged on two removable tool trays, one of it on both sides, and in the plastic tray with adjustable partitions in the bottom of the case. Further tools or accessories can be lodged in the tray until 60 mm height. The basic equipment for special operations at protective devices and alarm systems may efficiently be completed by special tools additionally recommended. The case has 2 locks.

Outside dimensions: 470 x 340 x 170 mm

Weight without tools: ca. 4.600 kg

Weight with tools: ca. 8.400 kg

Tool set:

No.	Description of individual tools	No.	Description of individual tools
2-265	2 Test prods , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire	6-600	Combination ring- and open-ended wrench , 7-piece set, CV, chrome-plated, 6,0, 7,0, 8,0, 9,0, 10,0, 11,0, 13,0 mm
2-701	Insertion tool with sensor for connecting the wires and simultaneously cutting of the residual wire	6-880	Hexagon wrench keys , 8-piece set in a wallet, 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 7/32", 1/4"
2-705	Contactless voltage detector VOLTtester	6-950	Ballpoint wrench keys , hexagon, 8-piece set in a wallet, 1,5, 2,0, 2,5, 3,0, 4,0, 5,0, 6,0, 8,0 mm
3-112-2	Side cutters , 120 mm, for soft wire up to 1.0 mm Ø; with rounded head, without side face, double leaf spring, chrome-plated, with dip insulation	6-995	TORX screwdrivers with bore-hole in the tip , 8-piece set in a box, T 9, T 10, T 15, T 20, T 25, T 27, T 30, T 40
3-0611	Crimping pliers , for BNC- and TNC-coaxial connectors	7-116	Engineer's hammer to DIN 1041, 300 g
13-906 VDE	VDE Side cutters , 160 mm, for steel wire up to 1.6 mm Ø; chrome-plated, VDE safty insulation	7-425	Dust brush
13-915 VDE	Telephone pliers , 160 mm, chrome-plated, VDE safty insulation	7-506	Roller tape measure , 2 m
13-927 VDE	Flat nose pliers , 160 mm, with long jaws, chrome-plated, VDE safty insulation	7-535	Spirit level , 225 mm long
13-936 VDE	Combination pliers , 160 mm, chrome-plated, VDE safty insulation	7-616	Pocket hack saw PUK , with adjustable handle in a wallet
4-431	Retaining screwdriver , for inserting and tightening slotted screws, blade made for CV, burnished, insulated, blade 100 x 3.0 mm	8-375	ERSA gas soldering iron , Independent 75
4-437	Retaining screwdriver , for inserting and tightening cross-recess screws size 1, blade made for CV, burnished, insulated	8-385	ERSA desoldering pump VAC X
5-505	Insulation stripping tool , with hook blade, for cable Ø 8 - 28 mm	14-651 VDE	Screwdriver , with VDE insulation, blade 75 x 2.5 mm
5-515	Universal blade knife	14-652 VDE	Screwdriver , with VDE insulation, blade 100 x 3.5 mm
5-531	Automatic wire stripper Super , for all common stranded and solid conductors of 0.2 - 6.0 mm ² , adjustable length stop of 5 - 12 mm, built-in side cutters for max. Ø 2 mm	14-653 VDE	Screwdriver , with VDE insulation, blade 100 x 4.0 mm
5-535	Coax cable stripper for Coax cabel Ø 4.8 - 7.5 mm	14-681 VDE	Cross-recess screwdriver , size 0, VDE, blade length 60 mm
6-103	Socket wrench , with special BERNSTEIN square handle, blade made from CV, chrome-plated, SW 4,5 mm	14-682 VDE	Cross-recess screwdriver , size 1, VDE, blade length 80 mm
6-104	Socket wrench , as above, AF 5.0 mm	14-683 VDE	Cross-recess screwdriver , size 2, VDE, blade length 100 mm
6-105	Socket wrench , as above, AF 5.5 mm	14-684 VDE	Cross-recess screwdriver , size 3, VDE, blade length 150 mm

To complete the set we recommend:

2270	Service Set ACCENT , 9-piece set with ESD tools
4-222	Screwdriver , blade 260 x 3.0 mm
4-227	Cross-recess screwdriver , size 1, blade length 300 mm
4-228	Cross-recess screwdriver , size 2, blade length 300 mm
4-920	Interchangeable screwdriver set with ESD-handle, 9-piece, Slot 1.5/3.0 mm, 2.0/3.5 mm und 2.5/4.0 mm, KS Gr. 000/00, 0/1, TORX T 5/T 6, T 7L/T 8L, T 9L/T 10L, ("L" with bore hole)