

Accessory / spare part, for plastic/metal range, round, 22 mm, 26x26mm, Lamp with base BA9s, incandescent lamp, 2 W, Length max. 28 mm, Piston diameter 10 mm, rated voltage 24 V AC/DC, clear,



Figure similar

General technical data:		
<b>Product designation</b>		incandescent lamp
<b>Type of light source</b>		filament lamp
<b>Color of the light source</b>		clear
<b>Mounting type</b>		BA 9s
<b>Product component</b>		
• series resistor		No
• diode		No
• lamp transformer		No
• Light source		Yes
<b>Type of voltage for actuation</b>		AC/DC
<b>Operating voltage</b>		
• at AC		
— at 50 Hz rated value	V	24 ... 24
— at 60 Hz rated value	V	24 ... 24
• at DC rated value	V	24 ... 24
<b>Relative positive tolerance of the operating voltage</b>	%	10

Relative negative tolerance of the operating voltage	%	-15
Consumed current for rated value of supply voltage maximum	mA	80
Type of electrical connection		Miscellaneous
Mounting type		miscellaneous

#### Certificates/approvals

General Product Approval

other

[Confirmation](#)



#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SX1344>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SX1344>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3SX1344>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SX1344&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SX1344&lang=en)

last modified:

10/23/2018