

## ANSMANN PRODUCT INFORMATION



**3** JAHRE  
YEARS  
GARANTIE  
WARRANTY

### ANSMANN WL4 Working Light

- Professional Working Lamp with the latest SMD LED technology
- Features a 100 lumens 1.5W spotlight on top of the housing
- Robust (shockproof to 1m) and splash-proof to IP54 housing with rubberized surface
- The base is 180° rotatable, in eight steps with lockable lamp handle
- Two 360° rotatable hooks on the back of the housing for flexible hanging options
- Two magnets on the back of the housing and one magnet on the bottom
- Built-in Li-Ion battery pack (3.7V / 2600mAh) with safety board
- Rechargeable via included USB mains power supply (100V-240V) using the included USB to Micro USB cable, or other USB power sources (PC, laptop, Powerbank, etc.)
- Charge state LED's on the back of the lamp unit
- Main lamp with 100% and 50% switch: 385 Lumens at 100%
- Operating time: approx. 4h (main lamp), approx. 11h (spotlight)
- Charging time: ca. 4h
- 3 years guarantee

### INFORMATION

**Product name:** WL4 Working Lamp  
**Article number:** 1600-0163-520  
**Accessories incl.:** USB Travel Charger with UK & EU plugs; USB to micro-USB charging cable

**Product:** 268 x 48 x 33mm (HxWxD)  
**Weight:** 340g + accessories: 470g  
**Packaging + product:** 365 x 116 x 110mm: 668g  
**Customs tariff number:** 94054039