

## DisplayPort 1.2 Cable with Latches - Certified, 2m

Product ID: DISPL2M



The DISPL2M 2m DisplayPort™ 1.2 Cable with latches provides a secure, connection between your DisplayPort-equipped devices and is capable of providing higher performance than either HDMI® or dual link DVI.

The DP cable supports high resolutions of up to 4k x 2k (4096 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The DISPL2M is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

### Certifications, Reports and Compatibility



### Applications

- Connecting a DisplayPort Display to a PC or other DisplayPort Source

### Features

- High-resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Backward compatible with DisplayPort 1.1
- Designed and manufactured to DisplayPort 1.2 standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Molded latching connectors with strain relief

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	19
<b>Connector(s)</b>	Connector A	1 - DisplayPort (20 pin) Latching Male
	Connector B	1 - DisplayPort (20 pin) Latching Male
<b>Physical Characteristics</b>	Cable Length	2 m [6.6 ft]
	Cable OD	7.3 mm [0.3 in]
	Color	Black
	Connector Style	Latching
	Product Length	2 m [6.6 ft]
	Product Weight	153.6 g [5.4 oz]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	162.6 g [5.7 oz]
<b>What's in the Box</b>	Included in Package	1 - 2m Latching DisplayPort 1.2 Cable

Product appearance and specifications are subject to change without notice.