

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1451300503](#)
Status: **Active**
Overview: Nano-Fit Power Connectors
Description: Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm, 5 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	145130
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Overmolded	No
Overview	Nano-Fit Power Connectors
Product Literature Order No	987651-6143
Product Name	Nano-Fit OTS
UPC	191130118915

Physical

Cable Length	300.00mm
Circuits (Loaded)	5
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	13.120/g
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm
Wire Size AWG	20
Wire/Cable Type	UL 1061


Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)

Material Info

Reference - Drawing Numbers

Sales Drawing	4000095320-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[145130](#) Series

Mates With

Nano-Fit Headers [105309](#) , [105311](#) , [105323](#)