

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1451350203](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf \(OTS\) Discrete Cable Assemblies](#)  
**Description:** Mini-Fit TPA2-to-Mini-Fit TPA2 Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 2 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">145135</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit TPA2 Both Ends
Overmolded	No
Overview	<a href="#">Off-the-Shelf (OTS) Discrete Cable Assemblies</a>
Product Literature Order No	987651-6143
Product Name	Mini-Fit TPA2
UPC	191130113460

**Physical**

Cable Length	300.00mm
Circuits (Loaded)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	12.794/g
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.98-3.14mm
Wire Size AWG	16
Wire/Cable Type	UL 1061


**Electrical**

Current - Maximum per Contact	11.0A
Voltage - Maximum	600V AC/DC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	4000095324-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[145135 Series](#)

**Mates With**

Mini-Fit TPA2 Plug Housing [200471](#) ,  
[200488](#) <br>Mini-Fit Jr. Plug Housing [5559](#)  
<br>Mini-Fit Jr. Headers [5566](#) , [5569](#)