

8 Outlet Metal Power Strip with 6ft Cord



Specifications

Max. Input Voltage	: 125V AC
Nominal Input Frequency	: 60Hz
Max. Output Power	: 1875W
Max. Line Current	: 15A
Circuit Breaker	: 15A 125V
Cord Type	: ETL/CETL SJT 14AWG/3C 60°C
Product Weight	: 45g (1FT cord)
Certifications	: ETL & CETL Listed
Standard	: UL1363, UL817
Colour	: Silver
Housing Material	: PC / Plastic UL94V-0
Enclosure Containment Design	: Screws
Outlet Design	: NEMA 5-15R, 8 holes grounded
AC Outlet	: 8 Outlets

Power Cord

Length Exposed (feet)	: 1.5ft - 25ft The length of a power-supply cord – as measured from the outside surface of the enclosure of the RPT to the plane of the face of the attachment plug – shall not exceed 25ft (7.62m) nor be less than 1.5ft (0.46m).
Cord Type	: ETL/CETL SJT 14AWG/3C 60°C
Enclosure Material	: PVC / Plastic UL94V-0
Plug Design	: NEMA 5-15P, Straight Plug, 45° Plug or 90° Plug
Standard	: UL817, UL62

Circuit Breaker

Switch	: 15A Breaker/Switch (On/off/reset switch on the top automatically switches off when an overload occurs.)
Circuit Breaker	: Overload Protection with switch (On/off/reset switch on the top automatically switches off when an overload occurs.)
Lighted	: Yes (The indicator light can be removed)
Colour	: Red (The indicator light can be removed)
Standard	: UL1077, UL1054

Environmental

Operating Temperature	: -0°C to +40°C
Conditions of Operation	: Indoor only

Part Number Table

Description	Part Number
Eight Outlet Metal Power Strip with 6ft Cord, Silver	28-21270