

Cable Marking Labels

- Clear overlamine is ideal for cable marking applications
- Resistant to oil, water and solvents
- Withstands temperatures from -40°F to 150°F
- Excellent for underground wiring



Catalog #	Material	Label Width Inch (mm)	Label Height Inch (mm)	Write-On Area Height	Max. Lines of Print	Max. Characters Across		Labels Per Roll
						Large	Small	
WML-511-292	Self-Laminating Vinyl	1.000 (25.4)	2.500 (63.5)	0.750 (19.05)	4	7	10	100
WML-517-292	Self-Laminating Vinyl	1.500 (38.1)	2.500 (63.5)	0.750 (19.05)	4	10	15	100
WML-711-292	Self-Laminating Vinyl	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	6	7	10	100
WML-717-292	Self-Laminating Vinyl	1.500 (38.1)	4.000 (101.6)	1.000 (25.4)	6	10	15	100

BradySleeve™ Wire Marking Sleeves

- Exclusive topcoat "soaks up" ink & retains it permanently, without additional curing
- Durable BradySleeve markers stand up to tough conditions



Catalog #	Approx. Wire Gauge	Min. Wire Dia. Inch (mm)	Max. Wire Dia. Inch (mm)	Sleeve Width Inch (mm)	Sleeve Height Inch (mm)	Max. Lines of Print	Max. Characters Across		Sleeves Per Roll
							Large	Small	
WMS-111-321	12-18	0.075 (1.90)	0.130 (3.30)	1.000 (25.40)	3.5(8.90)	1	7	10	500

Multiple-Across Wire Marking Strips (Approx. wire gauge - 10-14)

Catalog #	Label Material	Label Width Inch (mm)	Label Height Inch (mm)	Max. Lines of Print	Max. Characters Across		Number of Strips Across	Qty. Per Roll Strips/Sets
					Large	Small		
WML-505-499-2S*	Nylon Cloth	0.500 (12.7)	0.750 (19.05)	4	3	4	2	500-250
WML-505-502-2S*	White Vinyl Cloth	0.500 (12.7)	0.750 (19.05)	4	3	4	2	500/250

*Labels are scored in half, length-wise. The width is only .25"

Component & General Identification Labels

- Suitable for marking components in control panels, electronic components and circuit boards, faceplates and electrical receptacles
- Available in white vinyl cloth with a printable topcoat
- Withstands temperatures from -40°F to 180°F
- Resistant to oil, water and humidity
- Leaves no adhesive residue when removed
- Ideal for permanent or temporary applications



Catalog #	Label Material	Label Width Inch (mm)	Label Height Inch (mm)	Max. Lines of Print	Max. Characters Across		Labels Per Roll
					Large	Small	
CL-105-619	Polyester	0.500 (12.7)	0.275 (7.0)	1	3	4	500
CL-111-502	Vinyl Cloth	1.000 (25.4)	0.275 (7.0)	1	7	10	500
CL-111-619	Polyester	1.000 (25.4)	0.275 (7.0)	1	7	10	500
CL-111-969	Metalized Polyester	1.000 (25.4)	0.275 (7.0)	1	7	10	500
CL-117-619	Polyester	1.000 (25.4)	0.275 (7.0)	1	10	15	500
CL-311-502	Vinyl Cloth	1.000 (25.4)	0.500 (12.7)	3	7	10	500
CL-311-619	Polyester	1.000 (25.4)	0.500 (12.7)	3	7	10	500
CL-311-969	Metalized Polyester	1.000 (25.4)	0.500 (12.7)	3	7	10	500
CL-317-619	Polyester	1.500 (38.1)	0.500 (12.7)	3	10	15	500
CL-517-619	Polyester	1.500 (38.1)	0.750 (19.05)	4	10	15	250
CL-917-619	Polyester	1.500 (38.1)	1.250 (31.75)	8	10	15	250