

64mm Bi-Metal Holesaw

Code	BS30
Diameter	64mm (2 1/2")
Cutting Depth	35mm
Cutting Edge	HSS M3
Tooth Pitch	4 / 6 tpi Variable Pitch
Mount	7/16" - 5/8" UNF
Use With Arbor	Large Arbor - BA02 or BA05
Packaging	Cardboard Box
Pack Qty (Weight)	1 (188g)
Barcode	5039197009843



Description

Heavy Duty Holesaw for Industrial Use
HSS M3 Bi-Metal Cutting Edge provides Long Life
4/6tpi Variable Pitch Teeth enable Fast, Easy Cutting

Recommended Operating Speeds

Mild Steel - **135rpm** Stainless - **65rpm** Cast Iron - **85rpm**
Brass - **180rpm** Alu - **205rpm**
Wood & Plastic - **1850rpm**

Always use Cutting oil / spray when cutting metals

Applications

For cutting holes in Cast Iron, Stainless steel, steel, non-ferrous metals, wood and plastic.
Ideal for electrical, plumbing and production work

Suitable For

For use with all makes of mains powered and cordless rotary drills.