

## 102mm Bi-Metal Holesaw

Code	BS43
Diameter	102mm (4")
Cutting Depth	35mm
Cutting Edge	HSS M3
Tooth Pitch	4 / 6 tpi Variable Pitch
Mount	7/16" - 5/8" UNF
Use With Arbor	Large Arbor - BA02 or BA05
Packaging	Cardboard Box
Pack Qty (Weight)	1 (438g)
Barcode	5039197009973



## Description

Heavy Duty Holesaw for Industrial Use  
HSS M3 Bi-Metal Cutting Edge provides Long Life  
4/6tpi Variable Pitch Teeth enable Fast, Easy Cutting

## Recommended Operating Speeds

Mild Steel - **85rpm**      Stainless - **40rpm**      Cast Iron - **55rpm**  
Brass - **110rpm**      Alu - **130rpm**  
Wood & Plastic - **1000rpm**

**Always use Cutting oil / spray when cutting metals**

## Applications

For cutting holes in Cast Iron, Stainless steel, steel, non-ferrous metals, wood and plastic.  
Ideal for electrical, plumbing and production work

## Suitable For

For use with all makes of mains powered and cordless rotary drills.