

## 5.5mm x 93mm Cobalt Ground Jobber Drill Pack of 2

|                |                         |
|----------------|-------------------------|
| Code           | GCJT055                 |
| Size (Dia)     | 5.5mm                   |
| Overall Length | 93mm                    |
| Cutting Angle  | 135 Degree Split Point  |
| Pack Qty       | 2                       |
| Packaging      | Plastic Blister on Card |
| Weight         | 35g                     |
| Barcode        | 5039197071734           |



### Description

Professional quality, fully ground 5% (M35) Cobalt drill bits  
M35 (5% Cobalt) High Speed Steel increases Heat and Wear Resistance  
For drilling very hard, dense metals such as stainless steels, high tensile steels and cast iron.  
135° Split Point Tip for easy drill start without Skidding  
Manufactured to DIN338 standard

### Applications

For drilling high tensile steels, stainless steel, steel, cast iron and other "Tough to Drill" metals  
**Always use Cutting oil / spray when drilling metals**

### Suitable For

For use with all makes of pillar drills, mains powered and cordless rotary drills.