# GRM0335C1H160JA01# "#" indicates a package specification code.














< List of part numbers with package codes > GRM0335C1H160JA01D , GRM0335C1H160JA01W , GRM0335C1H160JA01J

#### **Shape**



L W	
L size	0.6 ±0.03mm
W size	0.3 ±0.03mm
Tsize	0.3 ±0.03mm
External terminal width e	0.1 to 0.2mm
Distance between external terminals g	0.2mm min.
Size code in inch(mm)	0201 (0603M)

### References

Packaging	Specifications	Minimum quantity
D	φ180mm Paper taping	15000
J	φ330mm Paper taping	50000
W	φ180mm Paper taping (W8P1*)  * Width: 8mm, Pocket pitch: 1mm	30000

Mass (typ.)	
1 piece	0.33mg
φ180mm Reel	118g

## **Specifications**

Capacitance	16pF ±5%
Rated voltage	50Vdc
Temperature characteristics (complied standard)	COG(EIA)
Temperature coefficient	0±30ppm/°C
Temperature range of temperature characteristics	25 to 125°C
Operating temperature range	-55 to 125°C

1 of 2




<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





<sup>2.</sup> This datasheet has only typical specifications because there is no space for detailed specifications.


#### Chart of characteristic data (The charts below may show another part number which shares its characteristics.)














2 of 2

**Attention** 

<sup>1.</sup>This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

<sup>2.</sup> This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.