



GML-5218

Order No.: 23.4570

Price upon request

PRODUCTINFOS

Electret gooseneck microphones with LED

- 3 replaceable microphone cartridges with different polar patterns (cardioid, supercardioid and omnidirectional)
- Excellent speech intelligibility
- -10 dB PAD switch
- Switchable low cut filter
- LED for indicating operating status
- Solid and high-quality workmanship to ensure a long service life
- Gooseneck with integrated 3-pole XLR plug
- Operation via external phantom power or microphone base ST-5030

TECHNICAL SPECIFICATIONS

GML-5218

Description

gooseneck microphone

GML-5218

Version	LED
Transmission method	cable
Polar pattern	cardioid/supercardioid/omnidir.
System	back electret
Audio frequency range	80-18,000 Hz
Nominal impedance	220 Ω \pm 30%
Sensitivity	16 mV/Pa
Max. sound pressure	125 dB
Power supply	DC 48 V phantom power
Admiss. ambient temp.	0-40 °C
Dimensions	615 mm
Weight	245 g
Connection	XLR, bal.