

Specification Sheet

Part Number: 156-00878



Outside Serrated Cable Tie & Edge Clip, 8.0" Long, EC24, 3-6 mm Panel, 50lb, PA66HS, Black, 500/pkg

Article Number	156-00878
Type	T50ROSEC24
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.•Edge Clip provides low insertion force and high extraction force ideal for assembly environments.•Two piece assembly allows the mount to slide along the strap ensuring proper orientation.•Cable tie is outside serrated to reduce bundle chafing.
Quantity Per	bag

Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description

Outside Serrated Cable Tie & Edge Clip, 8.0" Long, EC24, 3-6 mm Panel, 50lb, PA66HS, Black, 500/pkg

Global Part Name

T50ROSEC24-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

8.0

Length L (Metric)

200.0

Fixation Method

EdgeClip, sideways, assembled, 2 piece

Identification Plate Position

none

Releasable Closure

No

Variant

Outside Serrated

Width W (Imperial)

0.18

Width W (Metric)

4.6

Bundle Diameter Min (Imperial)

0.20

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

2.0

Bundle Diameter Max (Metric)

45.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Height H (Imperial)	0.05
Height H (Metric)	1.3
Panel Thickness Min(Imperial)	0.12
Panel Thickness Max(Imperial)	0.24
Panel Thickness Min (Metric)	3.0
Panel Thickness Max (Metric)	6.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	500

Package Quantity (Metric)

500

Customs Number

3926909987

Weight (Metric)

2.73