

Specification Sheet

Part Number: 156-00564



Cable Tie & Edge Clip, 8.0" Long, EC4A, 1–3 mm Panel, 45lb, PP/PA66HIRHSUV, Black, 500/pkg

Article Number	156-00564
Type	T50REC4A
Color	Black (BK)
Features & Benefits	• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments. • Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
Quantity Per	bag
Product Description	The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Short Description	Cable Tie & Edge Clip, 8.0" Long, EC4A, 1–3 mm Panel, 45lb, PP/PA66HIRHSUV, Black, 500/pkg
Global Part Name	T50REC4A-PP/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	25.0
Minimum Tensile Strength (Metric)	110
Length L (Imperial)	8.0
Length L (Metric)	202.0
Fixation Method	EdgeClip, top, assembled, 2 piece
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	0.05
Height H (Metric)	1.2
Panel Thickness Min(Imperial)	0.04
Panel Thickness Max(Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polypropylene (PP)
Material Shortcut	PP PA66HIRHS
Material Cable Tie	Polypropylene (PP)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +239°F (-40°C to +115°C) -40°F to +230°F (-40°C to +110°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	500

Package Quantity (Metric)

500

Customs Number

3926909987